

PNEUMATISKE VENTILER

DVA-A NC 1,5-0,12 PNEUM



- pneumatisk ventil
- Montering på ledningsnettet eller gass panel
- Egnet for ren acetylen
- Laget av forniklet messing

Laboratorier og analyse

Domains of applications

Designed for implementation of:

Pure acetylen

Except:

acetylen

Specifications

Working pressure 1.5 bar

Maximal Kv 0.12 m³/h*

Nominal diameter 4 mm

Tasso di fuga interno / esterno $\leq 3 \times 10^{-7}$ mbar.l/s di elio., Driftstemperatur: -20 ° C til + 50 ° C.

* Flow-hastighet koeffisient (Kv) i m³ / h av vannmengden for et tap av trykk på 1 bar i ventilen.


Materials

Body Forniklet messing

Hastelloy® er et registrert varemerke for Haynes International, Inc.

Dimensions

Length (L) : 49.5 mm
 Height (H) : 102 mm
 Depth (D) : 25 mm
 Ø1 : 45 mm
 Net weight : 0.5 kg



Operating instructions

OP 302

Connection

Inlet connection: G 3/8 BSPP kvinnelig
 Outlet connection: G 3/8 BSPP kvinnelig

Products

Product Number	Short Designation	Gas	Inlet Pressure	Inlet Fitting	Outlet Fitting	Material
163764	VALVE DVA-A NC 1,5-0,12 PNEUM	C2H2	1.5 bar	G 3/8 BSPP kvinnelig	G 3/8 BSPP kvinnelig	Messing

Options

	Product Number	Long designation
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE