

POENG FOR BRUK BS-LM 50-10-3.5



- Egnet for rene gasser
- Forkrommet messing

Laboratorier og analyse

Domains of applications

Designed for implementation of:
rene gasser

Specifications

Maximal inlet pressure at 15°C 50 bar

Outlet Pressure..... 1 til 10 bar


Nominal nitrogen flow 3.5 m³/h**

Safety Alert

⚠ Forsiktighet! I tilfelle av bruk av oksygen og oksiderende gasser, kan arbeidstrykket ikke overskride 25 bar.

Dimensions

Length (L) : 80 mm
Height (H) : 105 mm
Depth (D) : 140 mm
Ø1 : 50 mm
Net weight : 1.15 kg



Operating instructions

OP 250 - BS-LM

Connection

Inlet connection: 2 innløpsporter G 3/8 BSPP hunn
Outlet connection: 2 utløpsporter G 3/8 BSPP hunn

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
118168	POU BS.LM 50-10-3,5	blandinger, Rene gasser	50 bar	10 bar	3,5 Nm³/h	G 3/8 BSPP kvinnelig	G 3/8 BSPP kvinnelig	Messing
136930	PoU BS-LM 50-10-3 G3/8 M / KIT N°2	blandinger, Rene gasser	50 bar	10 bar	3,5 Nm³/h	G 3/8 BSPP M	KIT N ° 2	Messing
136932	POU BS-LM 50-10-3,5 G3/8 M - G3/8 AL F	blandinger, Rene gasser	50 bar	10 bar	3,5 Nm³/h	G 3/8 BSPP M	G 3/8 BSPP kvinnelig	Messing

Options

	Product Number	Long designation
	16516	CONN. G3/8 BSPP M NIP. F/PIPE Ø 4-6MM
	16521	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/8" OD Brass *Flat seal PTCFE
	16522	CONNECTION G 3/8" Male Compression Fitting 6 MM Br
	16523	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/4" OD Brass *Flat seal PTCFE
	16524	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 10mm OD Brass *Flat seal PTCFE
	16526	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 8mm OD Brass *Flat seal PTCFE
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE

	Product Number	Long designation
	16562	COMP. FITTING G3/8" 8 MM SS
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE
	19286	Connection G3/8 BSPP M NIP. Ø 8-10MM BR