

POENG FOR BRUK MODULGAS C3H8 5-4-15



- industrielt brukssted
- Stopp og justering av strømningshastigheten
- Egnet for propan
- Laget av messing

sveising, Industrial Process

Domains of applications

Designed for implementation of:
propan

Specifications

Maximal inlet pressure at 15°C..... 5 bar

Nominal nitrogen flow 15 m³/h*

Dimensions

Length (L) : 95 mm

Height (H) : 355 mm

Height (H1) : 245 mm

Depth (D) : 95 mm

Net weight : 2.7 kg

Operating instructions

OP 430 - Modulgas

Connection

Inlet connection: Inlet: G 3/8" hun

Outlet connection: Outlet: G 3/8" mannlig LH

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
45570	POU MODULGAS C3H8 5-4-15	C3H8	5 bar	4 bar	15 Nm ³ /h	G 3/8 BSPP kvinnelig	HF 6mm	Messing