

REGULATORER

PRIMEJET C2H2 25-1.5-5



- Regulator - Single scenen
- Montering på gassflasken
- Egnet for industriell acetylen
- Laget av messing

cutting, sveising

Domains of applications

PRIMEJET-serien tilbyr robuste ettrinnsregulatorer konstruert for maksimal sikkerhet og presisjon, fullt sertifisert i henhold til ISO 2503. PRIMEJET brukes til sveising, skjæring og for å skape atmosfærer innen ulike områder i industrien.

Designed for implementation of:

Industrial acetylen

Designed for:

acetylen

Except:

Alle andre gasser

Specifications

Maximal inlet pressure at 15°C 25 bar
Outlet Pressure 0,2 til 1,5 bar
Nominal nitrogen flow 5 m³/h*
Set pressure 1.5 bar

Driftstemperatur: -20 ° C til + 60 ° C.

*garantert ved maksimalt utløpstrykk P2 opp til et innløpstrykk P3 = 2P2 + 1 bar.

Materials

Body Messing
Seat CR
Diaphragm EPDM
Filter sintret bronse
Pressure gauge Ø 63mm, Kopperlegering

Highlights

Ergonomic: A robust and compact design of features paired with ergonomic handwheel to combine convenience with easy control.

Practical: Functional pressure gauges with triple units and color coding of the gases, allowing easy, accurate and safe identification of the settings.


Reliable: Flap box design intended to protect materials from possible returns.

Safety Alert

⚠ Advarsel! Må bruke passende personlig sikkerhetsutstyr (hansker, sveisebriller, forkle)

Dimensions

- Length (L)** : 290 mm
- Height (H)** : 210 mm
- Depth (D)** : 60 mm
- Ø1** : 63 mm
- Net weight** : 1.9 kg




Operating instructions

OP 110 - Primejet

Connection

- Inlet connection:** HP cylinder beslaget ifølge gass
- Outlet connection:** Utløp: G 3/8" eller M 16 hunn LH

Flow curve



Ordering Information

Regulatorne leveres med høytrykksinntak (NS) tilpasset type gass som benyttes og pigget slangekobling for fleksible slanger diameter 6 til 8 mm som skal monteres.

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Inlet Fitting Form	Outlet Fitting
204311	REG PRIMEJET A 25-1,5-5 TYPE H(NS)G3/8LH	C2H2	25 Bar	1,5 Bar	5 l/min	Type H (NS)	Wrench Brass	G 3/8 BSPP LH M

Options

Product Number	Long designation
163118	KIT Outlet CONNECTION PRIMEJET 50 bar G1/4 Nipple for welding 6mm