

MENGDEMÅLERE DYNAMAL 5L/MIN



- Mekanisk mengdemåler - Lavtrykk
- Montering på regulatoren eller ledningsnett
- Egnet for industrigasser
- Laget av lettmetall

Industrial Process

Domains of applications

Designed for implementation of:
industrigasser

Specifications

Maximal inlet pressure at 15°C 4 bar


Adjustable flow to 0 to 5 l/min

Maximal flow 5 l/min

Driftstemperatur: -20 ° C til + 50 ° C.

Dimensions

Length (L) : 56 mm
Height (H) : 121 mm
Depth (D) : 61 mm
Net weight : 0.4 kg



Connection

Inlet connection: En innløpsport G 3/8 BSPP hann

Outlet connection: En utløpsport M 12 x 125 hann

Products

Product Number	Short Designation	Gas	Inlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
15917	FLOW DYNAMAL N2 0,5-5l/min HF 4/6MM	N2	4 bar	5 l/min	G 3/8 BSPP M	HF 4 / 6mm	lettm metall
15929	FLOW DYNAMAL He 0,5-5l/min HF 4/6MM	He	4 bar	5 l/min	G 3/8 BSPP M	HF 4 / 6mm	lettm metall
15934	FLOW DYNAMAL H2 0,5-5l/min HF 4/6MM	H2	4 bar	5 l/min	G 3/8 BSPP M	HF 4 / 6mm	lettm metall