

LINJE~~POS=TRUNC REGULATO- RER

DCN800 AG 50-6-600



- Linje regulator - Single scenen
- Montering på ledningsnettet
- Egnet for industrigasser
- Laget av forniklet messing

Industrial Process

Domains of applications

Designed for implementation of:
industrigasser, metan

Specifications

Maximal inlet pressure at 15°C 50 bar

Outlet Pressure..... 0,8 til 6 bar

Nominal nitrogen flow 600 Nm³/h*

Driftstemperatur: -20 ° C til + 50 ° C.

* Nominell tilførsel av nitrogen ved 15 ° C.


Materials

Body	Forniklet messing
Seat	Messing
Main valve.....	Brass EPDM belagt
Diaphragm	NBR
Filter	Monel®
	Kobber legering mekanisme, Ø
Pressure gauge	50mm
Seal	Kobber, EPDM

Monel® er et varemerke for Special Metals Corporation.

Dimensions

Length (L) : 94 mm
Height (H) : 218 mm
Depth (D) : 127 mm
Ø1 : 50 mm
Net weight : 2.5 kg




Operating instructions

OP 212 - DCn800

Connection

Inlet connection: En innløpsport G 1" hunn
Outlet connection: En utløpsport G 1" hunn

Flow curve



Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
153739	REG DCN800 AG 50-6-600	Luft, CO2, inerte gasser, H2, O2	50 bar	6 bar	600 Nm³/h	G 1 BSPP F	G 1 BSPP F	Messing

Spare parts

Product Number		Long designation
153739	18525	Pressure Gauge 0-10 Bar Ø 50mm Back entry G1/4 for DCn100, 300, 500/2 and 800/2 Brass-Cr