

HP REGULATORER-MÅLERE DYNAREG 5L/MIN



- HP Regulator - mekanisk strømningsmåler - Single scenen
- Montering på regulatoren eller ledningsnettet
- Egnet for industrigasser
- Laget av en lett legering og forniklet messing

Industrial Process

Domains of applications

Designed for implementation of:
industrigasser

Specifications

Maximal inlet pressure at 15°C.....200 bar

Nominal nitrogen flow 5 l/min

Driftstemperatur: -20 ° C til + 50 ° C.

Materials

Body Forniklet messing
Seat PEEK
Main valve..... Messing
Flowmeter..... Lettmetall dial

Dimensions

Length (L) : 182 mm

Height (H) : 142 mm

Ø1 : 50 mm

Ø2 : 55 mm

Net weight : 1.3 kg

Connection

Outlet connection: Utløp: M 12 x 1 RH

Inlet connection: HP sylinter beslaget ifølge gass

Products

Product Number	Short Designation	Gas	Inlet Pressure	Flow	Inlet Fitting	Inlet Fitting Form	Outlet Fitting	Material
193364	FLOW-REG DYNAREG O2 5L/MIN TYPE F(NF)	O2	200 bar	5 l/min	NF F	Hånd Cr-Brass	HF 4 / 6mm	Messing