

LINJE~~POS=TRUNC REGULATO- RER

LH.V-L 200-10-10



- Regulator - Single scenen
- Montering på ledningsnettets eller gass panel
- Egnet for rene gasser og blandinger, ikke etsende
- Forkrommet messing

Laboratorier og analyse

Domains of applications

Designed for implementation of:

Ikke-etsende rene gasser opp til N60 inkludert ALPHAGAZ™ 1 & 2, Ikke-korrosive gasser med konsentrasjon som er større enn 1 ppm

Specifications

Maximal inlet pressure at 15°C 200 bar
Outlet Pressure 1 til 10 bar
Nominal nitrogen flow 2 Nm³/h*
Set pressure 16 bar

Materials



Body Forkrommet messing

Safety Alert

⚠ Forsiktighet! Ved bruk av brennbare gasser, skal alle purge og overløpsventiler samles opp.

Dimensions

Net weight : 1 kg



Operating instructions

OP 250 - LH.V-L

Connection

Inlet connection: En innløpsport \varnothing 16 x 1,336 SI hunn

Outlet connection: 2 utløpsporter G 3/8 BSPP hunn

Relief valve connection: Cr-messing Kompresjons monterings 6mm, messing Ferrules

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
152885	REG LH 200-10-10 V	blandinger	200 bar	10 bar	10 Nm ³ /h	\varnothing 16x1.336 SI hunn	G 3/8 BSPP kvinnelig	Messing

Options

	Product Number	Long designation
	16516	CONN. G3/8 BSPP M NIP. F/PIPE \varnothing 4-6MM
	16521	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/8" OD Brass *Flat seal PTCFE
	16522	CONNECTION G 3/8" Male Compression Fitting 6 MM Br
	16523	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/4" OD Brass *Flat seal PTCFE
	16524	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 10mm OD Brass *Flat seal PTCFE
	16526	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 8mm OD Brass *Flat seal PTCFE
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS

	Product Number	Long designation
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE
	19286	Connection G3/8 BSPP M NIP. \varnothing 8-10MM BR