

LINJE~~POS=TRUNC REGULATO- RER GM 15



Not Found

- Svært lav trykkregulator
- Montering på ledningsnettet
- Egnet for propan
- Laget av Zamak
- GM 15 pressure regulators are particularly suitable for controlling low-pressure artisanal, agricultural, and industrial processes that use LPG (butane, pro-

Industrial Process

Domains of applications

Designed for implementation of:
propan

Specifications


Maximal inlet pressure at 15°C 4 bar
Outlet Pressure 20 til 60 mbar
Nominal nitrogen flow 8.25 Nm³/h*

Materials

Body Zamak 3

Dimensions

Length (L) : 202 mm
Height (H) : 137 mm
Depth (D) : 92 mm
Depth (D1) : 56 mm
Net weight : 1.8 kg



Connection

Inlet connection: En innløpsport G 3/4" hann
Outlet connection: En utløpsport G 3/4" hann

Flow curve

Flow capacity (kg/h)	P1 Inletpressure			
	0.5	1	2	4
Model GM 15				
20 mbar	15	15	15	15
70 mbar	15	20	30	40

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
18158	REG GM 15	C3H8	4 bar	60 mbar	8.25 Nm³/h	G 3/4 BSPP mannlig	G 1/4" male	Zamak 3