

POENG FOR BRUK MODULGAS N2 15-10-30



- industrielt brukssted
- Stopp og justering av strømningshastigheten
- Egnet for nitrogen
- Laget av messing

sveising, Industrial Process

Domains of applications

Designed for implementation of:

Industri nøytrale gasser

Specifications

Maximal inlet pressure at 15°C 25 bar

Nominal nitrogen flow 15 m³/h*

Dimensions

Length (L) : 95 mm
Height (H) : 330 mm
Height (H1) : 245 mm
Depth (D) : 95 mm
Net weight : 2.4 kg

Operating instructions

OP 430 - Modulgas

Connection

Inlet connection: Inlet: G 3/8" hun
Outlet connection: Outlet: G 3/8" mannlig RH

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
45560	POU MODULGAS N2 15-10-30	N2	15 bar	10 bar	30 Nm³/h	G 3/8 BSPP kvinnelig	HF 6mm	Messing