


REGULATORER

HEPAL 12 200-8-15 FOOD



- Høytrykksregulator - Single scenen
- Montering på 200 bar gassflaske - tilbake oppføring
- Egnet for ALIGAL gasser
- Forkrommet messing

Mat, Drikke

Domains of applications

Designed for implementation of:

Gasser av ALIGAL™ -serien

Except:

Alle andre gasser

Specifications

Maximal inlet pressure at 15°C.....200 bar

Outlet Pressure.....8 bar

Nominal nitrogen flow 15 m³/h*

Set pressure 11 bar

Intern / ekstern lekkasjerate ≤ 10⁻⁸ mbar.l / s., Driftstemperatur: -20 ° C til + 50 ° C.

*garantert ved maksimalt utløpstrykk P2 opp til et innløpstrykk P3 = 2P2 + 1 bar.

Materials

Body Forkrommet messing

Seat Messing

Main valve..... Brass PCTFE belagt

Diaphragm Rustfritt stål

Kobber legering mekanisme, Ø

Pressure gauge 50mm, Forsegle i PA 6.6

Rustfritt stål, Seal i EPDM, Body i

Relief valve 303 rustfritt stål

Seal EPDM FDA

Monel® er et varemerke for Special Metals Corporation.

Safety Alert


⚠ Forsiktighet! Med karbondioksyd og argon, bruke en forvarmer ved høy strømning.

Highlights

En del av det nye matområdet

Dimensions

Length (L) : 107 mm
Height (H) : 98 mm
Depth (D) : 185 mm
Ø1 : 50 mm
Ø2 : 45 mm
Net weight : 1.31 kg




Operating instructions

OP 110 - Hepal 12 Food

Connection

Inlet connection: Innløp: HP sylinder forbindelse ifølge gassen
Outlet connection: En utløpsport G 3/8 BSPP hunn
Relief valve connection: Outlet port: G 1/4 BSPP kvinnelig

Flow curve



Products

Product Number	Short Designation	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Material
202309	REG HEPAL12 200-8-15 DIN10 W FOOD	200 bar	8 bar	15 Nm ³ /h	DIN 477-1 Nr. 10	Messing
202310	REG HEPAL12 200-8-15 DIN6 W FOOD	200 bar	8 bar	15 Nm ³ /h	DIN 477-1 Nr. 6	Messing

Options

Product Number	Long designation
19207	LEAK DETECTOR "1000 BULLES"

Spare parts

Product Number	Long designation
29053	FLAT SEAL in PA 6.6 20x12x2