

LINJE~~POS=TRUNC REGULATO- RER DACC 25-10-50 FOOD



- Linje regulator - Single scenen
- Montering på ledningsnettets eller gass panel
- Egnet for ALIGAL gasser
- Forkrommet messing

Mat, Drikke

Domains of applications

Designed for implementation of:

Gasser av ALIGAL™ -serien

Specifications

Maximal inlet pressure at 15°C 25 bar

Outlet Pressure..... 25 bar

Preset outlet pressure 10 bar

Nominal nitrogen flow 50 Nm³/h*

Mulig vakuüm for sporadiske utblåsninger, Tasso di fuga interno / esterno $\leq 3 \times 10^{-7}$ mbar.l/s di elio., Driftstemperatur: -20 ° C til + 50 ° C.

* Nominell tilførsel av nitrogen ved 15 ° C.

Materials

Body Forkrommet messing

Seat..... Messing

Main valve..... Messing EPDM FDA-belagt

Diaphragm 316L rustfritt stål

Pressure gauge Kopperlegering

Seal EPDM FDA

Highlights

En del av det nye matområdet

Dimensions


Height (H) : 130 mm

Depth (D) : 126 mm

Ø1 : 50 mm

Ø2 : 62 mm

Net weight : 1.3 kg



Operating instructions


OP 250 - DACC

Connection

Inlet connection: En innløpsport G 3/8 BSPP hunn

Outlet connection: En utløpsport G 3/8 BSPP hunn

Flow curve



Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
189209	REG DACC 25-10-50 FOOD	CO2, inerte gasser, O2	25 bar	10 bar	50 Nm³/h	G 3/8 BSPP kvinnelig	G 3/8 BSPP kvinnelig	Messing
203788	REG DACC 25-10-50 FOOD DB 6MM - DB 6MM	inerte gasser, O2	25 bar	10 bar	50 Nm³/h			Rustfritt stål
212192	REG DACC 25-10-50 FOOD CF 12MM - CF 12MM		25 bar	10 bar	50 Nm³/h			Messing

Options

	Product Number	Long designation
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE