

# POENG FOR BRUK MODULGAS 02 15-10-30



- industrielt brukssted
- Stopp og justering av strømningshastigheten
- Egnet for oksygen
- Laget av messing

sveising, Industrial Process

## Domains of applications

Designed for implementation of:  
Industrial oksygen

## Specifications

Maximal inlet pressure at 15°C.....25 bar

Nominal nitrogen flow ..... 15 m<sup>3</sup>/h\*

# Dimensions

Length (L) : 95 mm

Height (H) : 355 mm

Height (H1) : 245 mm

Depth (D) : 95 mm

Net weight : 2.7 kg

# Operating instructions

OP 430 - Modulgas

# Connection

Inlet connection: G 3/8 BSPP kvinnelig

Outlet connection: Outlet: G 3/8" mannlig RH

# Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
45567	POU MODULGAS O2 15-10-30	O2	15 bar	10 bar	30 Nm <sup>3</sup> /h	G 3/8 BSPP kvinnelig	HF 6mm	Messing