

LINJE~~POS=TRUNC REGULATO- RER DHP-L 200-50-10



- Egnet for rene gasser og blandinger, ikke etsende
- Forkrommet messing

Industrial Process, Laboratorier og analyse

Domains of applications

Designed for implementation of:

Ikke-etsende rene gasser opp til N60 inkludert ALPHAGAZ[™] 1 & 2, Ikke-korrosive gasser med konsentrasjon som er større enn 1 ppm

Except:

Nitrogendioksid, Karbondioksid, brennbare gasser

Specifications

Maximal inlet pressure at 15°C 200 bar

Outlet Pressure 5 til 50 bar

Nominal nitrogen flow 10 Nm³/h*

Materials


Body Forkrommet messing

INFO +

3.1 Certificate available on demand. Please contact Warehouse team before ordering.

Dimensions

Net weight : 1.8 kg




Operating instructions

OP 250 - DHP-L

Connection

Inlet connection: En innløpsport Ø 16 x 1,336 SI hunn
Outlet connection: 2 utløpsporter G 3/8 BSPP hunn

Flow curve



Products

Product Number	Short Designation	Gas	Inlet Fitting	Outlet Fitting	Material
15641	REG DHP 200-50-10	blandinger	Ø 16x1.336 SI hunn	G 3/8 BSPP kvinnelig	Messing

Options

	Product Number	Long designation		Product Number	Long designation
	16472	Connection 16X1,336 SI M - CF 6MM SS		16523	CONNECTION G 3/8 BSPP Male - CF 1/4" - Brass-Cr
	16474	Connection 16X1,336 SI M - CF 10MM SS		16524	CONNECTION G 3/8 BSPP Male - CF 10mm - Brass-Cr
	16516	CONNECTION G3/8 BSPP Male with Barb Hose for flexible pipe Ø Int. 4 to 6mm		16526	Connection G3/8 BSPP M - CF 8MM BRASS-CR
	16521	CONNECTION G 3/8 BSPP Male - CF 1/8" - Brass-Cr		16532	Kit n°2 : CF 6mm + CF 1/8" + Barbed hose 6mm
	16522	CONNECTION G 3/8" Male Compression Fitting 6 MM Brass Chrome GYROLOK		16558	Connection G3/8 BSPP M - CF 6MM SS

	Product Number	Long designation
	16562	COMP. FITTING G3/8" 8 MM SS
	16564	CONNECTION G 3/8 BSPP Male - CF 3/8" - Stainless Steel (Gyroløk)
	16565	Regulator HEPAL 100 AG 300-100-400 Inlet Cylinder Fitting NEN RU3
	16566	Connection G3/8 BSPP M - CF 1/8" SS

	Product Number	Long designation
	16567	Connection G3/8 BSPP M - CF 10MM SS
	16569	Connection G3/8 BSPP M - CF 12MM SS
	19286	Connection G3/8 BSPP M NIP. Ø 8-10MM BR

Spare parts

Product Number	SP Number	Long designation
15641	15969	PRESSURE GAUGE 0- 200/315 Bar Ø 50mm Vertical Entry M10x1 Brass-Cr - Body S.Steel
	16005	Manometer 0+70+100 BAR Ø50 vertikal justering. G1/4
	16218	Avlastningsventil Messing-Cr / NBR - 62 Bar Innløp G 3/8 BSPP M - Utløp G 3/8 BSPP F
	17130	O-RING in EPDM R9 10,5x2,7 mm EP851 for inlet connection brass - type C/B4 & E(NF)
	17141	Flat Seal PTFE (KEL-F®) 14,5X10X2