

LINJE~~POS=TRUNC REGULATO- RER DACC.S 25-10-50



- Linje regulator - Single scenen
- Montering på ledningsnettets eller gass panel
- Egnet for rene gasser
- Laget av rustfritt stål

Laboratorier og analyse

Domains of applications

Designed for implementation of:

Ikke-etsende rene gasser opp til N60 inkludert ALPHAGAZ™ 1 & 2, Ikke-korrosive gasser med konsentrasjon som er større enn 1 ppm

Except:

Nitrogenoksid

Specifications

Maximal inlet pressure at 15°C.....25 bar

Outlet Pressure.....0,7 til 10 bar

Nominal nitrogen flow50 Nm³/h*

Mulig vakuüm for sporadiske utblåsninger, Tasso di fuga interno / esterno $\leq 3 \times 10^{-7}$ mbar.l/s di elio., Driftstemperatur: -20 ° C til + 50 ° C.

* Nominell tilførsel av nitrogen ved 15 ° C.

Materials

Body 316 rustfritt stål

Seat 316L rustfritt stål

Balansert ventil i 316L rustfritt

Main valve..... stål FKM belagt


Diaphragm Hastelloy C®

Pressure gauge Rustfritt stål mekanisme, Ø 50mm

Seal PCTFE, FKM

Dimensions

Length (L) : 62 mm
 Height (H) : 125 mm
 Depth (D) : 125 mm
 Ø1 : 50 mm
 Net weight : 1.3 kg




Operating instructions

OP 250 - DACC.S

Connection

Inlet connection: En innløpsport G 3/8 BSPP hunn
Outlet connection: En utløpsport G 3/8 BSPP hunn

Flow curve



Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
15871	REG DACC.S 25-10-50	blandinger	25 bar	10 bar	50 Nm³/h	G 3/8 BSPP kvinnelig	G 3/8 BSPP kvinnelig	Rustfritt stål
87841	REG DACC.S 25-10-50 CF 6MM - CF 6MM	blandinger	25 bar	10 bar	50 Nm³/h	CF 6mm	CF 6mm	Rustfritt stål
15872	REG DACC.S 25-10-50 CF 10MM - CF 10MM	blandinger	25 bar	10 bar	50 Nm³/h	CF 10mm	G 3/8 BSPP kvinnelig	Rustfritt stål
87826	REG DACC.S 25-10-50 G3/8 AL M - CF 10MM	blandinger	25 bar	10 bar	50 Nm³/h	G 3/8 BSPP M	CF 10mm	Rustfritt stål
87829	REG DACC.S 25-10-50 G3/8 AL M	blandinger	25 bar	10 bar	50 Nm³/h	G 3/8 BSPP M	G 3/8 BSPP kvinnelig	Rustfritt stål

Options

	Product Number	Long designation
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE

	Product Number	Long designation
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE

Spare parts

Product Number		Long designation
15871	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTFE 14,5x10x2 for outlet port G3/8
87841	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTFE 14,5x10x2 for outlet port G3/8
15872	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTFE 14,5x10x2 for outlet port G3/8
87826	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTFE 14,5x10x2 for outlet port G3/8
87829	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTFE 14,5x10x2 for outlet port G3/8