

LINJE~~POS=TRUNC REGULATO- RER DACC 25-10-50



- Linje regulator - Single scenen
- Montering på ledningsnettets eller gass panel
- Egnet for rene gasser
- Forkrommet messing

Laboratorier og analyse, Industrial Process

Domains of applications

Designed for implementation of:

Ikke-etsende rene gasser opp til N60 inkludert ALPHAGAZ[™] 1 & 2, Ikke-korrosive gasser med konsentrasjon som er større enn 1 ppm

Except:

Karbondioksid

Specifications

Maximal inlet pressure at 15°C 25 bar

Outlet Pressure..... 0,7 til 10 bar

Nominal nitrogen flow 50 Nm³/h*

Mulig vakuum for sporadiske utblåsninger, Tasso di fuga interno / esterno $\leq 3 \times 10^{-7}$ mbar.l/s di elio., Drifttemperatur: -20 ° C til + 50 ° C.

* Nominell tilførsel av nitrogen ved 15 ° C.

Materials

Body Forkrommet messing

Seat Messing

Main valve..... Balansert ventil i messing NBR

Diaphragm belagt

Diaphragm Rustfritt stål

Pressure gauge Kobber legering mekanisme, Ø

Seal 50mm, Forsegle i PA 6.6

Seal NBR, PA 6.6

Dimensions

Length (L) : 45 mm
Height (H) : 97 mm
Depth (D) : 125 mm
Ø1 : 50 mm
Net weight : 1.3 kg




Operating instructions

OP 250 - DACC

Connection

Inlet connection: En innløpsport G 3/8 BSPP hunn
Outlet connection: En utløpsport G 3/8 BSPP hunn

Flow curve



Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
15869	REG DACC 25-10-50	andre CnHm, Rene gasser	25 bar	10 bar	50 Nm³/h	G 3/8 BSPP kvinnelig	G 3/8 BSPP kvinnelig	Messing
87859	REG DACC 25-10-50 CF 6MM - CF 6MM	andre CnHm, blandinger	25 bar	10 bar	50 Nm³/h	CF 6mm	CF 6mm	Messing
7977	REG DACC 25-10-50 CF 10MM - CF 10MM	andre CnHm, blandinger	25 bar	10 bar	50 Nm³/h	CF 10mm	CF 10mm	Messing
15870	REG DACC 25-10-50 SW 10MM - SW 10MM	andre CnHm, blandinger	25 bar	10 bar	50 Nm³/h	SW 10mm	SW 10mm	Messing
87852	REG DACC 25-10-50 G3/8 AL M - CF 10MM	Luft, C3H8, C2H4, H2, He, N2, N2O, CH4, Ar, O2	25 bar	10 bar	50 Nm³/h	G 3/8 BSPP M	CF 10mm	Messing
87855	REG DACC 25-10-50 G3/8 AL M	Luft, C3H8, C2H4, H2, He, N2, N2O, CH4, Ar, O2	25 bar	10 bar	50 Nm³/h	G 3/8 BSPP M	G 3/8 BSPP kvinnelig	Messing

Options

	Product Number	Long designation
	16516	CONN. G3/8 BSPP M NIP. F/PIPE Ø 4-6MM
	16521	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/8" OD Brass *Flat seal PTCFE
	16522	CONNECTION G 3/8" Male Compression Fitting 6 MM Br
	16523	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/4" OD Brass *Flat seal PTCFE
	16524	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 10mm OD Brass *Flat seal PTCFE
	16526	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 8mm OD Brass *Flat seal PTCFE

	Product Number	Long designation
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE
	19286	Connection G3/8 BSPP M NIP. Ø 8-10MM BR

Spare parts

Product Number		Long designation
15869	16001	Manometer -1 + 8 + 12 bar Ø50 vertikal M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
87859	16001	Manometer -1 + 8 + 12 bar Ø50 vertikal M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
7977	16001	Manometer -1 + 8 + 12 bar Ø50 vertikal M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
15870	16001	Manometer -1 + 8 + 12 bar Ø50 vertikal M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
87852	16001	Manometer -1 + 8 + 12 bar Ø50 vertikal M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
87855	16001	Manometer -1 + 8 + 12 bar Ø50 vertikal M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8